MOCKETT

PART #

PCS82C/5E

310.318.2491 • 800.523.1269 • www.mockett.com






Table thickness is 7/8 " MIN. to 1-11/16 " MAX.






Place metal clips in the slots on the side of the unit. (NOTE: Metal clips are for use in hard surface material only as an optional mounting means.)






Optional wire manager.

5




Secure unit by turning bottom wing clamp.

1



Make a cut out in the desired location on your work surface. Place near a power outlet and allow enough clearance for unit operation. $\underline{DO\ NOT}$ place unit where the cable is strained or trapped. Cut a hole at $9-13/32"\ X\ 4"$.

3



Guide the power cord through the cut out. Install the unit into the cut out and make sure it is fully leveled onto the surface.

